
NB300-312

Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB300-312

NB300-312

Synapsin I Antibody



Unit Size
0.05 ml

Concentration
This product is unpurified. The exact concentration of antibody is not quantifiable.

Storage
Store at -20C. Avoid freeze-thaw cycles.

Applications
WB

Species
Human, Mouse, Rat

Host
Rabbit

Clonality
Polyclonal

Purity
Whole antisera

Preservative
No Preservative

Marker
Synaptic Marker

Updated 3/9/2013 2.0

Specificity/Sensitivity
Specific for the ~78k synapsin I protein doublet. Immunolabeling blocked by preadsorption of the antibody with the protein used to generate the antibody.


Immunogen
Native protein purified from bovine brain

Recommended Dilutions
Western Blot 1:1000

Buffer
10 mM Hepes (pH7.5), 150 mM NaCl, 100 ug/ml BSA

Uses
This antibody has been tested in Western blot, detecting a band 78 kDa.

Images
Western Blot: Synapsin I Antibody [NB300-312] - Rat hippocampal lysate showing immunolabeling of the ~78k Synapsin I doublet, using NB300-312.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com