
NB300-740

Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB300-740

NB300-740

VGAT Antibody



Unit Size
0.1 ml

Concentration
Please see the vial label for concentration.

Storage
Store at -20C. Avoid freeze-thaw cycles.

Applications
WB

Species
Rat

Host
Rabbit

Clonality
Polyclonal

Purity
Affinity purified

Preservative
No Preservative

Updated 3/9/2013 2.0

Specificity/Sensitivity
Specific for the ~53k VGAT protein.

Immunogen
Synthetic peptide corresponding to amino acid residues from the N-terminal region conjugated to KLH

Recommended Dilutions
Western Blot 1:1000

Buffer
10 mM Hepes (pH7.5), 150 mM NaCl, 100 ug/ml BSA and 50% glycerol.

Uses
This antibody has been tested in Western blot. No other applications have been tested.

Images
Western Blot: VGAT Antibody [NB300-740] - Rat hippocampal lysate showing specific immunolabeling of the ~53k VGAT protein.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com