
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB200-133

NB200-133

eIF5A2 Antibody



Unit Size
0.1 mg

Concentration
1.0 mg/ml

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB, ELISA, IHC, IHC-Fr, IHC-P, IP

Species
Human

Host
Rabbit

Clonality
Polyclonal

Purity
Affinity purified

Preservative
0.02% Sodium Azide

Updated 3/9/2013 2.0

Specificity/Sensitivity
Reacts with the human EIF5 A2 protein. Cross-reactivity with human eIF5 A1 protein has been shown in endogenous samples.

Immunogen
A synthetic peptide representing the C-terminus of the Human EIF5 A2 protein.


Recommended Dilutions
Western Blot 1:500 - 1:1000, Immunohistochemistry-Frozen, Immunohistochemistry-Paraffin, ELISA, Immunoprecipitation, Immunohistochemistry

Buffer
PBS

Uses
Western Blotting

References (more available at www.novusbio.com/NB200-133)
Clement PM, Johansson HE, Wolff EC, Park MH. Differential expression of eIF5A-1 and eIF5A-2 in human cancer cells. FEBS J 273(6):1102-14. 2006 Mar. [PMID: 16519677

Images
Detection of endogenous and FLAG-tagged eIF5A1 in HeLa cells using NB 200-133 at a 1:1000 dilution



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com