
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB110-61682

NB110-61682

Somatostatin Antibody



Unit Size
0.05 ml

Concentration
Lyoph

Storage
Store at 4C short term. Aliquot and store at -80C long term. Avoid freeze-thaw cycles.

Applications
ELISA, IHC, IHC-P, RIA

Species
All Species

Host
Rabbit

Clonality
Polyclonal

Purity
Whole antisera

Preservative
No Preservative

Updated 3/9/2013 2.0

Specificity/Sensitivity
Specific detection of somatostatin by immunohistochemistry and radioimmunoassay in brain, retina and the gastrointestinal system in all species. Cross-reactivigy with other molecules: Gastrin 1.5%, C-peptide 0.007%, less than 0.001% for Human beta-endorphin.

Immunogen
A 14 amino acid synthetic Somatostatin peptide (H-AGCKNFFWKTFTSC-OH)conjugated to bovine thyroglobulin.

Recommended Dilutions
ELISA 1:100-1:10000, Immunohistochemistry-Paraffin 1:100-1:1000, Radioimmunoassay, Immunohistochemistry

Buffer
Lyophilized. Reconstitute with 0.05 ml sterile water.

Uses
ELISA, Immunohistochemistry-Paraffin, and Radioimmunoassay analysis.

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB110-61682

Notes
Add diH20 for desired concentration.

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com