
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB110-68281B

NB110-68281B

TRF1 Antibody (57-6) [Biotin]



Unit Size
0.1 ml

Concentration
1.5 mg/ml

Storage
Store at 4C in the dark.

Applications
WB, ELISA

Species
Human, Mouse, Rat, Primate

Host
Mouse

Clonality
Monoclonal

Isotype
IgG1 Kappa

Conjugate
Biotin

Purity
Protein G purified

Preservative
No Preservative

Marker
Telomere Marker

Updated 3/9/2013 2.0

Specificity/Sensitivity
TRF1 (57-6) - Telomere Marker

Immunogen
Recombinant TRF1

Recommended Dilutions
ELISA, Western Blot 0.5 ug/ml

Buffer
PBS

Uses
This antibody is useful for Western blot analysis where a band can be seen ~60 kDa. Past productions have been useful in ELISA.

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB110-68281B

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com