
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB110-68799

NB110-68799

vH RAS Antibody (H-Ras-03)



Unit Size
0.1 mg

Concentration
1.0 mg/ml

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB

Species
Human

Host
Mouse

Clonality
Monoclonal

Isotype
IgG1

Purity
Protein A purified

Preservative
15mM Sodium Azide

Updated 3/9/2013 2.0

Specificity/Sensitivity
The H-Ras-03 reacts with human H-Ras, an ubiquitously expressed 21 kDa intracellular protein. Although reactivity with other species has not been determined, it is probable as the epitope is highly conserved among animals.


Immunogen
Peptide corresponding to amino acids DIHQYREQIKRVKDSDDC of human H-Ras protein.

Recommended Dilutions
Western Blot 1:1000

Buffer
Phosphate buffered saline (PBS) pH 7.4

Uses
This antibody is useful for Western Blot and ELISA. Purity is > 95% (by SDS-PAGE).

Images
Western Blot: H-Ras Antibody (H-Ras-03) [NB110-68799] - Western Blotting analysis (reducing conditions) of H-Ras in whole cell lysate using anti-human H-Ras (H-Ras-03). Lane 1: HeLa human cervix carcinoma cell line Lane 2: K567 human leukemi... See more at www.novusbio.com/NB110-68799



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com