
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB110-82364C

NB110-82364C

TRPM2 Antibody [DyLight 650]



Unit Size
0.1 ml

Concentration
1.5 mg/ml

Storage
Store at 4C in the dark.

Applications
WB

Species
Mouse, Rat

Host
Rabbit

Clonality
Polyclonal

Conjugate
DyLight 650

Purity
Peptide affinity purified

Preservative
No Preservative

Updated 3/9/2013 2.0

Specificity/Sensitivity
TRPM2

Immunogen
Synthetic peptide made to an internal portion of the mouse protein (within residues 1200-1300). [Swiss-Prot# Q91YD4]

Recommended Dilutions
Western Blot 2.0 ug/ml,

Buffer
50mM sodium borate

Uses
This antibody is useful in Western blot, where a band is seen ~172 kDa.

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB110-82364C

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com