
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB110-93544

NB110-93544

TLR6 Antibody



Unit Size
0.1 ml

Concentration
1 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
WB

Species
Human, Mouse, Rat, Primate, Sheep

Molecular Weight
96kDa

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.1% Sodium Azide

Updated 3/9/2013 2.0


Immunogen
Synthetic peptide made to a C-terminal portion of the human TLR6 protein (within residues 700-796). [Swiss-Prot# Q9Y2C9]

Recommended Dilutions
Western Blot 1:1000-1:2000

Buffer
Tris-citrate/phosphate, pH 7-8

Uses
This TLR6 antibody is useful for Western blot, where a band is seen at ~96 kDa.

Images
Detection of TLR6 in Jurkat whole cell extract using NB110-93544.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com