
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB110-94158B

## NB110-94158B

# MAT2A Antibody [Biotin]



### Unit Size
0.1 ml

### Concentration
1.35 mg/ml

### Storage
Store at 4C in the dark.

### Applications
WB

### Species
Human, Mouse, Rat, Bovine, Primate

### Host
Rabbit

### Clonality
Polyclonal

### Conjugate
Biotin

### Purity
Peptide affinity purified

### Preservative
No Preservative

Updated 3/9/2013 2.0

### Specificity/Sensitivity
MAT2 alpha

### Immunogen
Synthetic peptide made to an N terminal portion of the human protein (within residues 1-100). [Swiss-Prot# P31153]

### Recommended Dilutions
Western Blot 1.0 ug/ml,

### Buffer
PBS

### Uses
This antibody is useful for Western blot, where a band is seen ~43 kDa.

### Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB110-94158B

*Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months.* ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

**Novus USA**
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

**Novus Canada**
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

**Novus Europe**
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com