
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB110-55376G

NB110-55376G

TARDBP Antibody [DyLight 488]



Unit Size
0.1 ml

Concentration
1.0 mg/ml

Storage
Store at 4C in the dark.

Applications
WB

Species
Human, Mouse, Chicken, Primate, Xenopus, Zebrafish

Host
Rabbit

Clonality
Polyclonal

Conjugate
DyLight 488

Purity
Immunogen affinity purified

Preservative
No Preservative

Updated 3/9/2013 2.0

Specificity/Sensitivity
TARDBP

Immunogen
A synthetic peptide to a C-terminal region [within residues 350-414] of the human TARDBP protein. [Swiss-Prot# Q13148]

Recommended Dilutions
Western Blot 0.5 to 2.0 ug/ ml

Buffer
50mM sodium borate

Uses
This antibody can be used for Western blot analysis where a band is seen at ~45 kDa, representing the human TARDBP protein.

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB110-55376G

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com