
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-93287

NB100-93287

EIF3J Antibody



Unit Size
0.1 ml

Concentration
1.0 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
WB, IHC-P, IP

Species
Human, Mouse

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.09% Sodium Azide

Updated 3/9/2013 2.0


Immunogen
The immunogen recognized by this antibody maps to a region between residue 208 and 258 of human eukaryotic translation initiation factor 3, subunit J (eukaryotic translation initiation factor 3, subunit 1) using the numbering given in entry NP_003749.2 (G

Recommended Dilutions
Immunohistochemistry-Paraffin, Immunoprecipitation, Western Blot 1:2000-1:10000


Buffer
Tris-citrate/phosphate buffer, pH 7 to 8

Uses
This antibody is useful for western blot and immunoprecipitation.

Images (more available at www.novusbio.com/NB100-93287)



Western Blot: EIF3J Antibody [NB100-93287] - Whole cell lysate from HeLa (5, 15 and 50 mcg for WB; 1 mg for IP, 20% of IP loaded) and 293T (T; 50 mcg) cells. NB100-93287 used for WB at 0.1 mcg/ml (A) and 1 mcg/ml (B) and used for IP at 3 mcg... See more at www.novusbio.com/NB100-93287



Immunohistochemistry-Paraffin: EIF3J Antibody [NB100-93287] - Human prostate carcinoma (left) and mouse teratoma (right). Antibody used at a dilution of 1:1,000.

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com