Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB110-40592

NB110-40592

SUPT5H Antibody

Unit Size
0.1 mg

Concentration
1.0 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
IP, WB (-)

Species
Human

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.09% Sodium Azide

Updated 3/9/2013 2.0


Immunogen
The immunogen recognized by this antibody maps to a region between residue 50 and 100 of human Suppressor of Ty 5 Homolog using the numbering given in entry NP_003160.2 (GeneID 6829).

Recommended Dilutions
Immunoprecipitation 2 -5 ug/mg lysate
Western Blot (Negative)

Buffer
Tris-citrate/phosphate buffer, pH 7 to 8

Uses
This antibody is useful for Immunoprecipitation. Western Blot is not recommended. Use NB110-40593.

Images
Immunoprecipitation: SUPT5H Antibody [NB110-40592] - Detection of Human SUPT5H by Western Blot of Immunoprecipitate. Samples: Whole cell lysate (1 mg for IP, 20% of IP loaded) from HeLa cells. Antibodies: Affinity purified rabbit anti-... See more at www.novusbio.com/NB110-40592



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com