
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-81657

NB100-81657

MBD2 Antibody



Unit Size
0.1 ml

Concentration
0.2 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
WB, IP

Species
Human, Mouse

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.09% Sodium Azide


Updated 3/9/2013 2.0

Immunogen
The immunogen recognized by this antibody maps to a region between residue 361 to 411 of human methyl-CpG binding domain protein 2 using the numbering given in entry NP_003918.1 (GeneID 8932).

Recommended Dilutions
Immunoprecipitation 2-5 ug/mg lysate, Western Blot 1:2000-1:10000

Buffer
Tris-buffered Saline and 0.1% BSA

Images
Western Blot: MBD2 Antibody [NB100-81657] - Detection of Human and Mouse MBD2 on HeLa whole cell lysate using NB100-81657. MBD2 was also immunoprecipitated by rabbit anti-MBD2 antibody NB100-81656.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com