
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-73229

## NB100-73229

# Yersinia Pestis V Antigen Antibody (Va48)



### Unit Size
0.2 mg

### Concentration
5.0 mg/ml

### Storage
Store at 4C. Do not freeze.

### Applications
WB, S-ELISA

### Species
Bacteria

### Host
Mouse

### Clonality
Monoclonal

### Isotype
IgG1

### Purity
Protein G purified

### Preservative
0.1% Sodium Azide

Updated 3/9/2013 2.0

### Specificity/Sensitivity
Y. pestis, V antigen

### Immunogen
Y. pestis, V antigen

### Recommended Dilutions
Sandwich ELISA
Western Blot

### Buffer
PBS, pH 7.4

### Uses
Recommended pair for sandwich immunoassay (capture-detection): NB100-73227 - NB100-73229

### Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB100-73229

*Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months.* ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

**Novus USA**
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

**Novus Canada**
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

**Novus Europe**
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com