
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-74539

NB100-74539

Somatostatin Receptor 4 Antibody



Unit Size
0.1 ml

Concentration
Concentrations vary lot to lot. See vial label for concentration.

Storage
Store at -20C. Avoid freeze-thaw cycles.

Applications
WB, ICC/IF, IHC, IHC-P

Species
Human

Host
Rabbit

Clonality
Polyclonal

Purity
Whole antisera

Preservative
0.05% Sodium Azide

Updated 3/9/2013 2.0

Immunogen
Synthetic peptide corresponding to residues C(366) Q Q E A L Q P E P G R K R I P L T R T T T F(388) of human SSTR4.

Recommended Dilutions
Western Blot 1:5000, Immunohistochemistry-Paraffin 1:2500, Immunocytochemistry/Immunofluorescence 1:5000, Immunohistochemistry

Buffer
Whole antisera.

Uses
In Western blot analysis of SSTR4 transfected HEK-293 cells this antibody detects a ~40-50 kDa protein representing SSTR4.

References
Arne G, Nilsson B, Dalmo J et al Gastrointestinal stromal tumors (GISTs) express somatostatin receptors and bind radiolabeled somatostatin analogs Acta Oncol 2012 Nov 1 [PMID: 23116418] (IHC, Human

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB100-74539

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com