
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-77278

NB100-77278

SMG1 Antibody



Unit Size
0.1 mg

Concentration
1.0 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
WB, IP, PLA

Species
Human

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.09% Sodium Azide

Updated 3/9/2013 2.0


Immunogen
The immunogen recognized by this antibody maps to a region between residue 1250 and 1300 of human PI-3-Kinase-related kinase SMG1 using the numbering given in entry NP_055907.3 (GeneID 23049).

Recommended Dilutions
Immunoprecipitation, Proximity Ligation Assay 1:1000-1:10000, Western Blot 1:1000-1:10000 immunoprecipitation 2-5 ug/mg lysate

Buffer
Tris-citrate/phosphate buffer, pH 7 to 8

Uses
This antibody is useful for western blot and immunoprecitation.

Images
Western Blot: SMG1 Antibody [NB100-77278] - HeLa whole cell lysate using NB100-77278. SMG1 was also immunoprecipitated by rabbit anti-SMG1 antibodies NB100-2320 and NB100-2321.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com