
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-55312

NB100-55312

SMARCC1 Antibody



Unit Size
0.1 ml

Concentration
0.2 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
WB, IP

Species
Human, Mouse

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.09% Sodium Azide

Updated 3/9/2013 2.0


Immunogen
The immunogen recognized by this antibody maps to a region between residue 300 and 350 of human SMARCC1/BAF155 using the numbering given in entry NP_003065.2 (GeneID 6599).

Recommended Dilutions
Immunoprecipitation 2 to 5 ug/mg lysate, Western Blot 1:2000 to 1:10000

Buffer
Tris-buffered Saline and 0.1% BSA

Uses
This antibody is useful for Western Blot and Immunoprecipitation .

Images
Western Blot: SMARCC1 Antibody [NB100-55312] - Detection of Human SMARCC1/BAF155 on HeLa whole cell lysate using NB100-55312.
SMARCC1/BAF155 was also IPed by rabbit anti-SMARCC1/BAF155 antibodies NB100-55313 and NB100-55314.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com