
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-55789

NB100-55789

HtrA2 Antibody (196C429) [Biotin]



Unit Size
0.1 mg

Concentration
0.5 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
ELISA

Species
Human, Mouse (Negative)

Host
Mouse

Clonality
Monoclonal

Isotype
IgG1 Kappa

Conjugate
Biotin

Purity
Protein G purified

Preservative
0.02% Sodium Azide

Updated 3/9/2013 2.0

Specificity/Sensitivity
HtrA2/Omi (196C429)

Immunogen
This monoclonal antibody was developed by immunizing mice with a synthetic peptide containing amino acids 335-350 of human Omi/HtrA2.

Recommended Dilutions
ELISA 2-3 ug/ml

Buffer
PBS

Uses
ELISA

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB100-55789

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com