
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-60455

NB100-60455

SGOL2 Antibody



Unit Size
0.1 ml

Concentration
0.2 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
WB, IP

Species
Human

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.09% Sodium Azide


Updated 3/9/2013 2.0

Immunogen
The immunogen recognized by this antibody maps to a region between residue 750 and 800 of human shugoshin-like 2 using the numbering given in entry NP_689737.3 (GeneID 151246).

Recommended Dilutions
Immunoprecipitation 2-5 ug/mg lysate, Western Blot 1:2000-1:10000

Buffer
Tris-buffered Saline and 0.1% BSA

Images
Western Blot: SGOL2 Antibody [NB100-60455] - Detection of Human SGO2 on HeLa whole cell lysate using NB100-60455. SGO2 was also immunoprecipitated by rabbit anti-SGO2 antibody NB100-60454.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com