
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-2385C

NB100-2385C

S-arrestin Antibody (PDS-1) [DyLight 650]



Unit Size
0.1 ml

Concentration
0.77 mg/ml

Storage
Store at 4C in the dark.

Applications
WB, ICC/IF, IHC, IHC-Fr

Species
Human, Bovine, Porcine

Host
Mouse

Clonality
Monoclonal

Isotype
IgG1

Conjugate
DyLight 650

Purity
IgG purified

Preservative
No Preservative

Updated 3/9/2013 2.0

Specificity/Sensitivity
This is specific for arrestin protein.

Immunogen
Porcine retinal S-antigen (arrestin). [Swiss-Prot# P79260]

Recommended Dilutions
Western Blot, Immunohistochemistry-Frozen 1:100, Immunocytochemistry/Immunofluorescence, Immunohistochemistry

Buffer
50mM sodium borate

Uses
The MW is ~45 kDa. It may be useful for immunopurification of arrestin [see product specific reference (1)]. No other application has been tested. The investigator should determine the optimal working dilution for a specific application.

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB100-2385C

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com