
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-2582

NB100-2582

Spt6 Antibody



Unit Size
0.1 ml

Concentration
0.2 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
WB, IHC, IHC-P, IP

Species
Human, Mouse

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.09% Sodium Azide

Updated 3/9/2013 2.0


Immunogen
The immunogen recognized by this antibody maps to a region between residue 425 and 475 of human Suppressor of Ty 6 Homolog using the numbering given in entry NP_003161.2 (GeneID 6830).

Recommended Dilutions
Immunohistochemistry, Immunohistochemistry-Paraffin 1:100 - 1:500, Immunoprecipitation 2 -5 ug/mg lysate, Western Blot 1:2000 to 1:10000

Buffer
Tris-buffered Saline and 0.1% BSA

Uses
This antibody is useful for Western Blot and Immunoprecipitation

Images (more available at www.novusbio.com/NB100-2582)



Western Blot: Spt6 Antibody [NB100-2582] - Detection of Human SUPT6H on HeLa whole cell lysate using NB100-2582. SUPT6H was also immunoprecipitated by another rabbit anti-SUPT6H antibody.

Immunohistochemistry-Paraffin: Spt6 Antibody [NB100-2582] - FFPE section of mouse squamous cell carcinoma. Affinity purified rabbit anti-SUPT6H used at a dilution of 1:500.

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com