
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-1620

NB100-1620

Mu Opioid Receptor Antibody



Unit Size
0.05 ml

Concentration
This product is unpurified. The exact concentration of antibody is not quantifiable.

Storage
Store at -20C. Avoid freeze-thaw cycles.

Applications
WB, ICC/IF, IHC, IHC-Fr

Species
Human, Mouse, Rat, Primate

Host
Rabbit

Clonality
Polyclonal

Purity
Whole antisera

Preservative
0.05% Sodium Azide

Updated 3/9/2013 2.0

Specificity/Sensitivity
Mu Opioid Receptor


Immunogen
Synthetic peptide: NHQLENLEAETAPLP, corresponding to C terminal amino acids 384-398 of Rat Mu Opioid Receptor.

Recommended Dilutions
Immunohistochemistry-Frozen 1/2500 - 1/5000, Western Blot, Immunocytochemistry/Immunofluorescence 1:100-1:2000, Immunohistochemistry

Buffer
Whole Serum

Uses
Dilutions listed only as a recommendation. Optimal dilution should be determined by investigator.

Images
Immunohistochemistry: Mu Opioid Receptor Antibody [NB100-1620] - Striatum



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com