
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/34770002

34770002

EGFR Antibody



Unit Size
0.05 mg

Concentration
Please see the vial label for concentration.

Storage
Store at -20C. Avoid freeze-thaw cycles.

Applications
WB, ELISA

Species
Human

Host
Rabbit

Clonality
Polyclonal

Purity
Affinity purified

Preservative
No Preservative

Updated 3/9/2013 2.0

Specificity/Sensitivity
This product is specific for Human EGFR.


Immunogen
This antibody is specific for the Middle Region of the target protein.

Recommended Dilutions
ELISA, Western Blot 1:5000-1:20000

Buffer
20 mM Potassium Phosphate, 150 mM Sodium Chloride, pH 7.0

Uses
This antibody is useful in ELISA and Western Blot.

Images
ELISA: EGFR Antibody [34770002]



Notes
Manufactured by SDIX's proprietary Genomic Antibody Technology™. GAT FAQs.

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com