
NB100-288

Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-288

NB100-288

MCM2 Antibody



Unit Size
0.1 ml

Concentration
1.0 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
WB, IP, PLA

Species
Human, Xenopus

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.1% Sodium Azide

Updated 3/9/2013 2.0


Immunogen
A 37-amino acid synthetic peptide, which represented a portion of human Minichromosome Maintenance Deficient 2 encoded within exon 2 (LocusLink ID 4171).

Recommended Dilutions
Immunoprecipitation 2 -5 ug//mg lysate, Proximity Ligation Assay 1:1000 - 1:10000, Western Blot 1:1000 - 1:10000

Buffer
Tris-citrate/phosphate buffer, pH 7 to 8

References (more available at www.novusbio.com/NB100-288)
Kadara H, Behrens C, Yuan P et al A five-gene and corresponding protein signature for stage-I lung adenocarcinoma prognosis Clin Cancer Res 2011 Mar 15 [PMID: 21163870] (IHC, Human

Images
Western Blot: MCM2 Antibody [NB100-288] - RIPA extract (50 mcg for WB; 7 mg for CoIP) from HeLa cells. Affinity purified rabbit anti-MCM2 used at 0.2 mcg/ml for WB and 20 mcg/7mg extract for IP



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com