9F, No. 108, Jhouzih St., Taipei, Taiwan
Tel: + 886-2-8751-1888 Fax: + 886-2-6602-1218
E-mail: sales@abnova.com

Datasheet

NEK10 monoclonal antibody (M01), clone 1C9

Catalog Number: H00152110-M01

Regulation Status: For research use only (RUO)

Product Description: Mouse monoclonal antibody raised against a partial recombinant NEK10.

Clone Name: 1C9

Immunogen: NEK10 (NP_689747, 211 a.a. ~ 300 a.a) partial recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.

Sequence:
RYFMEANRNTVTCHHELAVLSHETFEKASLSSSSSGA
ASLKSELSESADLPPEGFQASYGKDEDRACDEILSDD
NFNLENAEKDTYSEVD

Host: Mouse

Reactivity: Human,Mouse

Applications: ELISA, IF, S-ELISA, WB-Ce, WB-Re, WB-Tr
(See our web site product page for detailed applications information)

Protocols: See our web site at http://www.abnova.com/support/protocols.asp or product page for detailed protocols

Isotype: IgG2a Kappa

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 152110

Gene Symbol: NEK10

Gene Alias: FLJ32685