9F, No. 108, Jhouzih St., Taipei, Taiwan
Tel: + 886-2-8751-1888 Fax: + 886-2-6602-1218
E-mail: sales@abnova.com

Datasheet

Phenyl-acetic acid polyclonal antibody

Catalog Number: PAB14695

Regulation Status: For research use only (RUO)

Product Description: Rat polyclonal antibody raised against Phenyl-acetic acid.

Immunogen: Phenyl-acetic acids conjugated with carrier protein.

Host: Rat

Applications: ELISA, IHC
(See our web site product page for detailed applications information)

Protocols: See our web site at http://www.abnova.com/support/protocols.asp or product page for detailed protocols

Form: Lyophilized

Purification: Ammonium sulfate precipitation

Recommend Usage: ELISA (1:2000-1:10000)
Immunohistochemistry (1:1000-1:5000)
The optimal working dilution should be determined by the end user.

Storage Buffer: Lyophilized from PBS, pH 7.4

Storage Instruction: Store at 4°C on dry atmosphere.
After reconstitution with 50 uL of distilled water and 50 uL of glycerol, store at -20°C for 2 years.
Aliquot to avoid repeated freezing and thawing.