ProSci

prosci-inc.com

HIGH PERFORMANCE ANTIBODIES ... AND MORE


ProSci Incorporated
12170 Flint Place
Poway, CA 92064

Toll Free: +1 (888) 513 9525
Local: +1 (858) 513 2638
Fax: +1 (858) 513 2692

techsupport@prosci-inc.com

RHOA Antibody [1B12]

CATALOG NUMBER: 51-881



Immunohistochemistry of human breast tissue stained using RHOA Monoclonal Antibody.

Specifications

SPECIES REACTIVITY:	Human
TESTED APPLICATIONS:	ELISA, IF, IHC, WB
APPLICATIONS:	RHOA antibody can be used in Western Blot starting at 1:200, and immunohistochemistry starting at 5 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
IMMUNOGEN:	RHOA (AAH01360, 1 a.a. ~ 194 a.a) full length recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.
HOST SPECIES:	Mouse

Properties

PURIFICATION:	Protein A Column
PHYSICAL STATE:	Liquid
BUFFER:	PBS, pH 7.2
CONCENTRATION:	0.5 mg/ml
STORAGE CONDITIONS:	Aliquot and store RHOA antibody at -20 ˚C or -80 ˚C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Monoclonal
ISOTYPE:	IgG1,l
CONJUGATE:	Unconjugated

Additional Info

ALTERNATE NAMES:	RHOA, ARH12, ARHA, Aplysia ras-related homolog 12, H12, Oncogene RHO H12, Rho cDNA clone 12, RHO12, RHOH12, Ras homolog family member A, Small GTP binding protein RhoA, Transforming protein RhoA
ACCESSION NO.:	P61586
PROTEIN GI NO.:	47606458
OFFICIAL SYMBOL:	RHOA
GENE ID:	387

Background

FOR RESEARCH USE ONLY

December 13, 2016