Anti-RAT IgG F(ab')2 (RABBIT) Antibody - 112-4104

Code: 112-4104 **Size:** 2 mL

Product Description: Anti-RAT IgG F(ab')2 (RABBIT) Antibody - 112-4104

Concentration: 80 mg/mL by Refractometry

PhysicalState: Lyophilized

Label	Unconjugated
Host	Rabbit
Buffer	0.01 M Sodium Phosphate, 0.15 M Sodium Chloride, pH 7.2
Stabilizer	None
Preservative	None
Storage Condition	Store vial at 4° C prior to restoration. For extended storage aliquot contents and freeze at -20° C or below. Avoid cycles of freezing and thawing. Centrifuge product if not completely clear after standing at room temperature. This product is stable for several weeks at 4° C as an undiluted liquid. Dilute only prior to immediate use.
Purity And Specificity	This product was prepared from monospecific antiserum by a delipidation and defibrination. Assay by immunoelectrophoresis resulted in a single precipitin arc against Rat IgG, Rat IgG F(ab')2 and Rat Serum. No reaction was observed against Rat IgG F(c).
Assay Dilutions	User Optimized
ELISA	1:20,000 - 1:100,000
Immunohistochemistry	1:1,000 - 1:5,000
WESTERN BLOT	1:2,000 - 1:10,000
IHC	1:1,000 - 1:5,000
OTHER ASSAYS	User Optimized
Expiration	Expiration date is one (1) year from date of opening.
Immunogen	Rat IgG F(ab')2 fragment

Related Products

610-4302	Anti-MOUSE IgG (H&L) (RABBIT) Antibody Peroxidase Conjugated - 610-4302
611-1302	Anti-RABBIT IgG (H&L) (GOAT) Antibody Peroxidase Conjugated - 611-1302
B304	NORMAL GOAT SERUM (NGS) - B304
BSA-50	BOVINE SERUM ALBUMIN - Fraction V (Immunoglobulin and Protease Free) - BSA-50

Related Links

Disclaimer

This product is for research use only and is not intended for therapeutic or diagnostic applications. Please contact a technical service representative for more information. All products of animal origin manufactured by Rockland Immunochemicals are derived from starting materials of North American origin. Collection was performed in United States Department of Agriculture (USDA) inspected facilities and all materials have been inspected and certified to be free of disease and suitable for exportation. All properties listed are typical characteristics and are not specifications. All suggestions and data are offered in good faith but without guarantee as conditions and methods of use of our products are beyond our control. All claims must be made within 30 days following the date of delivery. The prospective user must determine the suitability of our materials before adopting them on a commercial scale. Suggested uses of our products are not recommendations to use our products in violation of any patent or as a license under any patent of Rockland Immunochemicals, Inc. If you require a commercial license to use this material and do not have one, then return this material, unopened to: Rockland Inc., P.O. BOX 5199, Limerick, Pennsylvania, USA.