spectrum™
chemicals & laboratory products

Item Number	H1393
Item	Hypromellose, Substitution Type 2208, USP
CAS Number	9004-65-3
Molecular Formula	
Molecular Weight	

Viscosity of a 2% Aqueous Solution @ 20°C..... 75,000-140,000 mPa·s

Assay:

|Methoxy Groups..... 19.0-24.0%

|Hydroxypropoxy Groups..... 4.0-12.0%

pH..... 5.0-8.0

MAXIMUM LIMITS

Loss on Drying..... 5.0%

Residue on Ignition..... 1.5%

Heavy Metals..... 20 ppm

Residual Solvents..... To pass test

Spectrum Chemicals & Laboratory Products

Corporate Headquarters:
14422 S. San Pedro St.
Gardena, CA 90248

East Coast Facility:
755 Jersey Ave.
New Brunswick, NJ 08901

(800) 813-1514 • (310) 516-8000 • Fax (310) 516-9843