Thermo SCIENTIFIC

Part of Thermo Fisher Scientifi
The world leader in serving science

Material Safety Data Sheet

Protein A/G Ultralink® Resin

1. Product and company identification

Product name : Protein A/G Ultralink® Resin

Supplier : Thermo Fisher Scientific
Pierce Biotechnology
P.O. Box 117
Rockford, IL 61105
United States
815.968.0747 or
800.874.3723

Manufacturer : Thermo Fisher Scientific
Pierce Biotechnology
P.O. Box 117
Rockford, IL 61105
United States
815.968.0747 or
800.874.3723

Code : 0053132 0053133

MSDS # : 2341

Validation date : 7/13/2011.

Print date : 7/13/2011.

Responsible name : MSDS Specialist

In case of emergency : **CHEMTREC:
800.424.9300
OUTSIDE US:
703.527.3887**

Material uses : **Refer to the instruction booklet for proper and intended use. Otherwise, contact supplier for specific applications.**

Product type : Liquid.

2. Hazards identification

Emergency overview

Physical state : Liquid. [Suspension.]

Color : White.

Signal word : WARNING!

Hazard statements : CAUSES RESPIRATORY TRACT AND EYE IRRITATION.

Precautionary measures : Avoid breathing vapor or mist. Use only with adequate ventilation. Avoid contact with eyes. Keep container tightly closed. Wash thoroughly after handling.

OSHA/HCS status : This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

Routes of entry : Dermal contact. Eye contact. Inhalation. Ingestion.

Potential acute health effects

Inhalation : Severely irritating to the respiratory system.

Ingestion : No known significant effects or critical hazards.

Skin : No known significant effects or critical hazards.

Eyes : Severely irritating to eyes. Risk of serious damage to eyes.

Potential chronic health effects

Chronic effects : No known significant effects or critical hazards.

Life Science Research
Pierce Biotechnology Inc.
PO Box 117
3747 N. Meridian Road
Rockford, IL
61105
(815) 968-0747
(815) 968-7316 Fax
www.thermo.com

2. Hazards identification

Carcinogenicity : No known significant effects or critical hazards.

Mutagenicity : No known significant effects or critical hazards.

Teratogenicity : No known significant effects or critical hazards.

Developmental effects : No known significant effects or critical hazards.

Fertility effects : No known significant effects or critical hazards.

Over-exposure signs/symptoms

Inhalation : Adverse symptoms may include the following:
respiratory tract irritation
coughing

Ingestion : No specific data.

Skin : No specific data.

Eyes : Adverse symptoms may include the following:
pain or irritation
watering
redness

Medical conditions aggravated by over-exposure : None known.

See toxicological information (Section 11)

3. Composition/information on ingredients

United States

Name	CAS number	%
Azlactone Acrylamide Copolymer	-	10 - 20

Canada

Name	CAS number	%
Azlactone Acrylamide Copolymer	-	10 - 20

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section.

4. First aid measures

Eye contact : Check for and remove any contact lenses. Immediately flush eyes with plenty of water for at least 15 minutes, occasionally lifting the upper and lower eyelids. Get medical attention immediately.

Skin contact : In case of contact, immediately flush skin with plenty of water for at least 15 minutes while removing contaminated clothing and shoes. Wash clothing before reuse. Clean shoes thoroughly before reuse. Get medical attention immediately.

Inhalation : Move exposed person to fresh air. If not breathing, if breathing is irregular or if respiratory arrest occurs, provide artificial respiration or oxygen by trained personnel. Loosen tight clothing such as a collar, tie, belt or waistband. Get medical attention immediately.

Ingestion : Wash out mouth with water. Do not induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Get medical attention immediately.

Life Science Research
Pierce Biotechnology Inc.
PO Box 117
3747 N. Meridian Road
Rockford, IL
61105
(815) 968-0747
(815) 968-7316 Fax
www.thermo.com

4. First aid measures

Protection of first-aiders : No action shall be taken involving any personal risk or without suitable training. If it is suspected that fumes are still present, the rescuer should wear an appropriate mask or self-contained breathing apparatus. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation.

Notes to physician : No specific treatment. Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.

5. Fire-fighting measures

Flammability of the product : In a fire or if heated, a pressure increase will occur and the container may burst.

Extinguishing media

Suitable : Use an extinguishing agent suitable for the surrounding fire.

Not suitable : None known.

Special exposure hazards : Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training.

Hazardous thermal decomposition products : No specific data.

Special protective equipment for fire-fighters : Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode.

6. Accidental release measures

Personal precautions : No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilled material. Avoid breathing vapor or mist. Provide adequate ventilation. Wear appropriate respirator when ventilation is inadequate. Put on appropriate personal protective equipment (see Section 8).

Environmental precautions : Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).

Methods for cleaning up

Small spill : Stop leak if without risk. Move containers from spill area. Dilute with water and mop up if water-soluble. Alternatively, or if water-insoluble, absorb with an inert dry material and place in an appropriate waste disposal container. Dispose of via a licensed waste disposal contractor.

Large spill : Stop leak if without risk. Move containers from spill area. Approach release from upwind. Prevent entry into sewers, water courses, basements or confined areas. Wash spillages into an effluent treatment plant or proceed as follows. Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations (see section 13). Dispose of via a licensed waste disposal contractor. Contaminated absorbent material may pose the same hazard as the spilled product. Note: see section 1 for emergency contact information and section 13 for waste disposal.

Life Science Research PO Box 117 Rockford, IL (815) 968-0747 www.thermo.com
Pierce Biotechnology Inc. 3747 N. Meridian Road 61105 (815) 968-7316 Fax

Protein A/G Ultralink® Resin

7. Handling and storage

Handling : Put on appropriate personal protective equipment (see Section 8). Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. Remove contaminated clothing and protective equipment before entering eating areas. Do not ingest. Avoid contact with eyes, skin and clothing. Avoid breathing vapor or mist. Use only with adequate ventilation. Wear appropriate respirator when ventilation is inadequate. Keep in the original container or an approved alternative made from a compatible material, kept tightly closed when not in use. Empty containers retain product residue and can be hazardous. Do not reuse container.

Storage : Store between the following temperatures: 2 to 8°C (35.6 to 46.4°F). Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see section 10) and food and drink. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabeled containers. Use appropriate containment to avoid environmental contamination.

8. Exposure controls/personal protection

Canada

Occupational exposure limits
No exposure limit value known.

Consult local authorities for acceptable exposure limits.

Recommended monitoring procedures : If this product contains ingredients with exposure limits, personal, workplace atmosphere or biological monitoring may be required to determine the effectiveness of the ventilation or other control measures and/or the necessity to use respiratory protective equipment.

Engineering measures : Use only with adequate ventilation. If user operations generate dust, fumes, gas, vapor or mist, use process enclosures, local exhaust ventilation or other engineering controls to keep worker exposure to airborne contaminants below any recommended or statutory limits.

Hygiene measures : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.

Personal protection

Respiratory : Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

Hands : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Eyes : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists or dusts.

Skin : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

Environmental exposure controls : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.

Life Science Research PO Box 117 Rockford, IL (815) 968-0747 www.thermo.com
Pierce Biotechnology Inc. 3747 N. Meridian Road 61105 (815) 968-7316 Fax

8. Exposure controls/personal protection

9. Physical and chemical properties

Physical state : Liquid. [Suspension.]

Flash point : [Product does not sustain combustion.]

Color : White.

Dispersibility properties : Easily dispersible in the following materials: cold water and hot water.

10. Stability and reactivity

Chemical stability : The product is stable.

Conditions to avoid : No specific data.

Incompatible materials : No specific data.

Hazardous decomposition products : Under normal conditions of storage and use, hazardous decomposition products should not be produced.

Possibility of hazardous reactions : Under normal conditions of storage and use, hazardous reactions will not occur.

11. Toxicological information

United States

Acute toxicity

Conclusion/Summary : Not available.

Chronic toxicity

Conclusion/Summary : Not available.

Irritation/Corrosion

Conclusion/Summary : Not available.

Sensitizer

Conclusion/Summary : Not available.

Carcinogenicity

Conclusion/Summary : Not available.

Mutagenicity

Conclusion/Summary : Not available.

Teratogenicity

Conclusion/Summary : Not available.

Reproductive toxicity

Conclusion/Summary : Not available.

Canada

Acute toxicity

Conclusion/Summary : Not available.

Chronic toxicity

Conclusion/Summary : Not available.

Irritation/Corrosion

Conclusion/Summary : Not available.

Sensitizer

Conclusion/Summary : Not available.

Carcinogenicity

Life Science Research Pierce Biotechnology Inc. PO Box 117 3747 N. Meridian Road Rockford, IL 61105 (815) 968-0747 (815) 968-7316 Fax www.thermo.com

Protein A/G Ultralink® Resin

11. Toxicological information

Conclusion/Summary : Not available.

Mutagenicity

Conclusion/Summary : Not available.

Teratogenicity

Conclusion/Summary : Not available.

Reproductive toxicity

Conclusion/Summary : Not available.

12. Ecological information

Ecotoxicity : No known significant effects or critical hazards.

United States

Aquatic ecotoxicity

Conclusion/Summary : Not available.

Persistence/degradability

Conclusion/Summary : Not available.

Canada

Aquatic ecotoxicity

Conclusion/Summary : Not available.

Persistence/degradability

Conclusion/Summary : Not available.

Other adverse effects : No known significant effects or critical hazards.

13. Disposal considerations

Waste disposal : The generation of waste should be avoided or minimized wherever possible. Significant quantities of waste product residues should not be disposed of via the foul sewer but processed in a suitable effluent treatment plant. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible. This material and its container must be disposed of in a safe way. Care should be taken when handling emptied containers that have not been cleaned or rinsed out. Empty containers or liners may retain some product residues. Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

Disposal should be in accordance with applicable regional, national and local laws and regulations.

Refer to Section 7: HANDLING AND STORAGE and Section 8: EXPOSURE CONTROLS/PERSONAL PROTECTION for additional handling information and protection of employees.

14. Transport information

Regulatory information	UN number	Proper shipping name	Classes	PG*
DOT Classification	Not regulated.	-	-	-
IATA-DGR Class	Not regulated.	-	-	-

Life Science Research Pierce Biotechnology Inc. PO Box 117 3747 N. Meridian Road Rockford, IL 61105 (815) 968-0747 (815) 968-7316 Fax www.thermo.com

14. Transport information

PG* : Packing group

15. Regulatory information

United States

HCS Classification : Irritating material

U.S. Federal regulations : **TSCA 8(a) PAIR**: Glycols, polyethylene, mono(p-(1,1,3,3-tetramethylbutyl)phenyl) ether; Glycols, polyethylene, mono(p-(1,1,3,3-tetramethylbutyl)phenyl) ether
TSCA 8(a) IUR Exempt/Partial exemption: Not determined
United States inventory (TSCA 8b): Not determined.

SARA 302/304/311/312 extremely hazardous substances: No products were found.
SARA 302/304 emergency planning and notification: No products were found.
SARA 302/304/311/312 hazardous chemicals: No products were found.
SARA 311/312 MSDS distribution - chemical inventory - hazard identification: No products were found.

Clean Water Act (CWA) 311: disodium hydrogenorthophosphate

Clean Air Act Section 112(b) Hazardous Air Pollutants (HAPs) : Not listed

Clean Air Act Section 602 Class I Substances : Not listed

Clean Air Act Section 602 Class II Substances : Not listed

DEA List I Chemicals (Precursor Chemicals) : Not listed

DEA List II Chemicals (Essential Chemicals) : Not listed

State regulations

Massachusetts : None of the components are listed.

New York : None of the components are listed.

New Jersey : None of the components are listed.

Pennsylvania : None of the components are listed.

California Prop. 65

WARNING: This product contains less than 0.1% of a chemical known to the State of California to cause cancer.
WARNING: This product contains less than 1% of a chemical known to the State of California to cause birth defects or other reproductive harm.

Ingredient name	Cancer	Reproductive	No significant risk level	Maximum acceptable dosage level
1,4-Dioxane	Yes.	No.	30 µg/day (ingestion) 30 µg/day (inhalation)	No.
Ethylene oxide	Yes.	Yes.	2 µg/day (ingestion) 2 µg/day (inhalation)	20 µg/day (ingestion) 20 µg/day (inhalation)

United States inventory (TSCA 8b) : Not determined.

Life Science Research Pierce Biotechnology Inc. PO Box 117 3747 N. Meridian Road Rockford, IL 61105 (815) 968-0747 (815) 968-7316 Fax www.thermo.com

Protein A/G Ultralink® Resin

15. Regulatory information

Canada

WHMIS (Canada) : Class D-2B: Material causing other toxic effects (Toxic).

Canadian lists

Canadian NPRI : None of the components are listed.

CEPA Toxic substances : None of the components are listed.

Canada inventory : Not determined.

This product has been classified in accordance with the hazard criteria of the Controlled Products Regulations and the MSDS contains all the information required by the Controlled Products Regulations.

International regulations

International lists : **Australia inventory (AICS)**: Not determined.
China inventory (IECSC): Not determined.
Japan inventory: Not determined.
Korea inventory: Not determined.
New Zealand Inventory of Chemicals (NZIoC): Not determined.
Philippines inventory (PICCS): Not determined.

16. Other information

Label requirements : CAUSES RESPIRATORY TRACT AND EYE IRRITATION.

Hazardous Material Information System (U.S.A.) :



The customer is responsible for determining the PPE code for this material.

National Fire Protection Association (U.S.A.) :

Date of printing : **7/13/2011.**

Date of issue : 7/13/2011.

Date of previous issue : No previous validation.

Version : 1

Prepared by : MSDS Specialist

Indicates information that has changed from previously issued version.

Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein.
Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.

Life Science Research Pierce Biotechnology Inc. PO Box 117 3747 N. Meridian Road Rockford, IL 61105 (815) 968-0747 (815) 968-7316 Fax www.thermo.com