
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP2-12006

NBP2-12006

CD137 Antibody (RM0068-4G33)



Unit Size
0.1 mg

Concentration
Lyoph

Storage
Store at 4C. Do not freeze.

Applications
WB, FLOW

Species
Mouse

Host
Rat

Clonality
Monoclonal

Isotype
IgG2

Purity
>95% pure by SDS-PAGE

Preservative
No Preservative

Updated 3/9/2013 2.0

Immunogen
Mouse CD137

Recommended Dilutions
Flow Cytometry
Western Blot

Buffer
Lyophilized in PBS

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP2-12006

Notes
Storage: Room temperature or 4 degree before antibody is re-suspended; -20 or -80 for longer period of storage after re-suspension.

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com