
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NLS1942

# NLS1942

# CELSR2 Antibody



## Unit Size
0.05 ml

## Concentration
Concentrations vary lot to lot. See vial label for concentration.

## Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

## Applications
IHC, IHC-P

## Species
Human

## Host
Rabbit

## Clonality
Polyclonal

## Purity
Immunogen affinity purified

## Preservative
0.01% Sodium Azide

Updated 3/9/2013 2.0

## Specificity/Sensitivity
CELSR2


## Immunogen
Synthetic peptide [KLH conjugated] made to the N-term extracellular

## Recommended Dilutions
Immunohistochemistry-Paraffin 15-20 ug/ml, Immunohistochemistry

## Buffer
PBS [pH7.7]

## Uses
This antibody is useful for Immunohistochemistry-Paraffin.

## Images
Breast, Lobular Epithelium



*Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months.* ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

**Novus USA**
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

**Novus Canada**
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

**Novus Europe**
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com