
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-99631

NBP1-99631

UBE2H Protein



Unit Size
0.1 mg

Concentration
1 mg/ml

Storage
Store at -80C. Avoid freeze-thaw cycles.

Species
Human

Purity
>95% pure by SDS-PAGE

Updated 3/9/2013 2.0

Specificity/Sensitivity
Unit Definition:N/A

Immunogen
Source: E. coli
Endotoxin Level: N/A
Activity (Specifications/test method):N/A
Biological activity:N/A
Results:N/A
Binding Capacity:N/A
Amino acid Sequence:N/A

Buffer
Supplied at a concentration of 1.0 in 20 mM Tris-HCl, pH 7.5, containing 0.5 mM DTT.
N/A

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP1-99631

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com