
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-97656

NBP1-97656

BCMA Antibody (human) [PE]



Unit Size
0.05 mg

Concentration
1.0 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
FLOW

Species
Human, Mouse (Negative)

Host
Rat

Clonality
Monoclonal

Isotype
IgG1

Conjugate
PE

Purity
Protein G purified

Preservative
0.02% Sodium Azide

Updated 3/9/2013 2.0


Immunogen
Recombinant human BCMA extracellular domain (aa 2-54).

Recommended Dilutions
Flow Cytometry 1:100

Buffer
PBS

Uses
Detects a band of ~40 kDa by Western blot.

Images
Flow Cytometry: BCMA Antibody (human) [PE] [NBP1-97656] - Analysis of 10^6 U266 cells stained using BCMA (human), mAb (Vicky-1) (PE conjugate) at a concentration of 10ug/ml.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com