Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-79604

# NBP1-79604

# VSTM2A Antibody

## Unit Size
0.05 mg

## Concentration
Lyoph

## Storage
Store at -20C. Avoid freeze-thaw cycles.

## Applications
WB

## Species
Human, Mouse, Rat, Bovine, Canine, Chicken, Zebrafish

## Host
Rabbit

## Clonality
Polyclonal

## Purity
Peptide affinity purified

## Preservative
No Preservative

Updated 3/9/2013 2.0

## Immunogen
Synthetic peptide directed towards the middle region of human VSTM2AThe immunogen for this antibody is VSTM2A.

## Recommended Dilutions
Western Blot 1:1000

## Buffer
PBS & 2% Sucrose lyophilized with the antibody.Centrifuge the vial of lyoph antibody at 12,000 x g for 20 seconds. Add 50ul of distilled water. Vortex followed by centrifuge again to pellet the solution.Final concentration is 1 mg/ml in PBS buffer

## Uses
This is a rabbit polyclonal antibody against VSTM2A and was validated on Western blot.

## Images
Western Blot: VSTM2A Antibody [NBP1-79604] - Human Brain lysate, concentration 0.2-1 ug/ml.

*Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months.* ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

**Novus USA**
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

**Novus Canada**
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

**Novus Europe**
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com