Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-78424

NBP1-78424

TetR Antibody



Unit Size
0.1 ml

Concentration
1.13 mg/ml

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB

Species
Non-species specific

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.05% Sodium Azide

Updated 3/9/2013 2.0

Immunogen
A synthetic peptide made to an N-terminal portion of Escherichia coli TetR protein (between residues 1-50) [UniProt P04483]

Recommended Dilutions
Western Blot 1:1000

Buffer
PBS, 30% glycerol

Uses
This TetR antibody is useful for Western blot.

Images
Western Blot: TetR Antibody [NBP1-78424] - Analysis of TetR in 23kDa recombinant protein. Note the presence of a dimer.

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com