
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-76718

# NBP1-76718

# TIP47 Antibody



## Unit Size
0.1 mg

## Concentration
1 mg/ml

## Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

## Applications
WB, ELISA, IHC, IHC-P

## Species
Human, Rat

## Host
Rabbit

## Clonality
Polyclonal

## Purity
Affinity purified

## Preservative
0.02% Sodium Azide

Updated 3/9/2013 2.0

## Immunogen
Antibody was raised against a 14 amino acid peptide from near the carboxy terminus of human TIP47.

## Recommended Dilutions
ELISA, Immunohistochemistry, Immunohistochemistry-Paraffin, Western Blot

## Buffer
PBS containing 0.02% sodium azide.

## Uses
ELISA, Western Blot, Immunohistochemistry-Paraffin

## Images
Western Blot: TIP47 Antibody [NBP1-76718] - Daudi cell lysate with TIP47 antibody at (A) 0.5 and (B) 1 ug/ml.

Immunohistochemistry-Paraffin: TIP47 Antibody [NBP1-76718] - Rat liver tissue with TIP47 antibody at 10 ug/ml.

*Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months.* ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

**Novus USA**
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

**Novus Canada**
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

**Novus Europe**
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com