
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-47454

NBP1-47454

MATK Antibody (9D7)



Unit Size
0.1 ml

Concentration
Please see the vial label for concentration.

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB, ELISA

Species
Human

Host
Mouse

Clonality
Monoclonal

Isotype
IgG1

Purity
Affinity purified

Preservative
0.03% Sodium Azide

Updated 3/9/2013 2.0

Immunogen
Purified recombinant fragment of human MATK expressed in E. Coli.


Recommended Dilutions
Western Blot 1: 500 - 1:2000
ELISA 1:10000

Buffer
PBS with 50% Glycerol


Uses
This antibody is useful in Western Blot, ELISA.

Images

Western Blot: MATK Antibody (9D7) [NBP1-47454] - Western blot analysis using anti-MATK mAb against K562 cell lysate (1).



Flow cytometry / FACS analysis: MATK Antibody (9D7) [NBP1-47454] - Flow cytometric analysis of K562 cells using anti-MATK mAb (green) and negative control (purple).



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com