
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-47555

NBP1-47555

B Raf Antibody (1H12F1)



Unit Size
0.1 ml

Concentration
This product is unpurified. The exact concentration of antibody is not quantifiable.

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB, ELISA, IHC, IHC-Fr, IHC-P

Species
Human

Host
Mouse

Clonality
Monoclonal

Isotype
IgG1

Purity
Ascites

Preservative
0.03% Sodium Azide

Updated 3/9/2013 2.0

Immunogen
Purified recombinant fragment of BRAF expressed in E. Coli.

Recommended Dilutions
Western Blot 1: 500 -1: 2000, Immunohistochemistry-Frozen 1:200 - 1:1000, Immunohistochemistry-Paraffin 1:200 - 1000, ELISA 1:10000, Immunohistochemistry


Buffer
Ascites

Uses
This antibody is useful in Western Blot, Immunohistochemistry-Frozen, Immunohistochemistry-Paraffin, ELISA.

Images (more available at www.novusbio.com/NBP1-47555)



Western Blot: B Raf Antibody (1H12F1, 1H12G10,1F12F11C9) [NBP1-47555] - Western blot analysis using BRAF mouse mAb against HEK293T cells transfected with the pCMV6-ENTRY control (1) and pCMV6-ENTRY Braf cDNA (2).



Immunohistochemistry-Paraffin: B Raf Antibody (1H12F1, 1H12G10,1F12F11C9) [NBP1-47555] - Immunohistochemical analysis of paraffin-embedded human bladder carcinoma tissue(left) and lung carcinoma tissue(right) showing cytoplasmic localization... See more at www.novusbio.com/NBP1-47555

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com