
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-45867

NBP1-45867

SP3 Antibody



Unit Size
0.1 mg

Concentration
0.5 mg/ml

Storage
Store at -20C. Avoid freeze-thaw cycles.

Applications
WB

Species
Human, Mouse, Rat

Host
Rabbit

Clonality
Polyclonal

Purity
Affinity purified

Preservative
0.01% Thimerosal

Updated 3/9/2013 2.0


Immunogen
Synthetic peptide surrounding amino acid 766 of mouse Sp3.

Recommended Dilutions
Western Blot

Buffer
phosphate-buffered saline (PBS) containing 30% glycerol, 0.5% BSA

Uses
Western blot analysis (0.5-4ug/ml). However, the optimal conditions should be determined individually. Other applications have not been tested. The antibody detects ~86-100 kDa Sp3 in samples from human, mouse and rat origins.

Images
Western Blot: SP3 Antibody [NBP1-45867] - Analysis of Sp3 using lysates from Jurkat cells (Lane 1& 2), 3T3 cells (Lane 3) and Rat kidney (Lane 4).



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com