
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-45884

NBP1-45884

TEM8 Antibody



Unit Size
0.1 mg

Concentration
Please see the vial label for concentration.

Storage
Store at -20C. Avoid freeze-thaw cycles.

Applications
WB

Species
Human, Mouse, Rat

Host
Rabbit

Clonality
Polyclonal

Purity
Affinity purified

Preservative
0.01% Thimerosal

Updated 3/9/2013 2.0


Immunogen
Synthetic peptide corresponding to residues surrounding amino acids 484 of Mouse TEM8.

Recommended Dilutions
Western Blot

Buffer
phosphate-buffered saline (PBS) containing 30% glycerol, 0.5% BSA

Uses
Western blotting (0.5-4ug/ml). However, the optimal concentrations should be determined individually. The antibody recognizes ~80-85 kDa doublet of TME8 in samples from human, mouse and rat origins. Reactivity to other species has not been tested.

Images
Western Blot: TEM8 Antibody [NBP1-45884] - Analysis of TEM8 using lysates from rat kidney (Lane 1), mouse small intestine (Lane 2), and Jurkat cells (Lane 3).



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com