Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-28873

NBP1-28873

Wnt5a Antibody (6F2)

Unit Size
0.1 ml

Concentration
This product is unpurified. The exact concentration of antibody is not quantifiable.

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB, ELISA, ICC/IF, IHC, IHC-P

Species
Human

Molecular Weight
42.3kDa kDa

Host
Mouse

Clonality
Monoclonal

Isotype
IgG1

Purity
Ascites

Preservative
0.03% Sodium Azide

Updated 3/9/2013 2.0

Specificity/Sensitivity
Specific for WNT5A.


Immunogen
Purified recombinant fragment of WNT5A expressed in E. Coli.

Recommended Dilutions
ELISA 1:10000, Western Blot 1:500 - 1:1000, Immunohistochemistry-Paraffin 1:200-1:1000, Immunocytochemistry/Immunofluorescence 1:200-1:1000, Immunohistochemistry


Buffer
Ascitic fluid

Uses
Western Blot and ELISA

Images (more available at www.novusbio.com/NBP1-28873)



Western Blot: Wnt5a Antibody (6F2) [NBP1-28873] - Western blot analysis using WNT5A mouse mAb against HEK293 (1) and WNT5A-hIgGFc transfected HEK293 cell lysate (2).



Immunohistochemistry-Paraffin: Wnt5a Antibody (6F2) [NBP1-28873] - Immunohistochemical analysis of paraffin-embedded human lung cancer (A), thyroid cancer (B), lymph node (C) and brain (D) showing cytoplasmic and extracellular matrix localiz... See more at www.novusbio.com/NBP1-28873

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com