
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-30931

NBP1-30931

Tetraspanin-1 Antibody



Unit Size
0.1 mg

Concentration
Concentrations vary lot to lot. See vial label for concentration.

Storage
Store at -20C. Avoid freeze-thaw cycles.

Applications
WB, DB, IHC-P

Species
Human

Host
Rabbit

Clonality
Polyclonal

Purity
Affinity purified

Preservative
0.01% Thimerosal

Updated 3/9/2013 2.0


Immunogen
Synthetic peptide corresponding to a region within amino acids 132 and 227 of Tetraspan 1 (Uniprot ID#O60635)

Recommended Dilutions
Dot Blot, Immunohistochemistry-Paraffin, Western Blot 1:500-1:3000


Buffer
0.1M Tris, 0.1M Glycine, 10% Glycerol (pH7.0).

Uses
Dot blot, Western blot

Images
Western Blot: Tetraspanin-1 Antibody [NBP1-30931] - Sample(30 ug whole cell lysate)A: H129912% SDS PAGE, antibody diluted at 1:500.



Immunohistochemistry-Paraffin: Tetraspanin-1 Antibody [NBP1-30931] - Paraffin-embedded Colon ca, using antibody at 1:500 dilution.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com