
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-28123

NBP1-28123

Integrin alpha E Antibody (2E7)



Unit Size
0.5 mg

Concentration
0.5 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
FLOW, IHC, IHC-Fr, In vitro, IP

Species
Mouse

Host
Armenian Hamster

Clonality
Monoclonal

Isotype
IgG

Purity
IgG purified

Preservative
No Preservative

Updated 3/9/2013 2.0

Specificity/Sensitivity
The CD103/alpha IELbeta7 integrin complex (Mr 160 and 115 kDa peptides).

Immunogen
The CD103/alpha IELbeta7 integrin complex (Mw 160 and 115 kDa peptides).

Recommended Dilutions
Flow Cytometry, Immunoprecipitation, Immunohistochemistry-Frozen, In vitro assay, Immunohistochemistry

Buffer
100 mM borate buffered saline, pH 8.2

Uses
Flow Cytometry, Immunoprecipitation, Immunohistochemistry-Frozen and In vitro assay

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP1-28123

Notes
Inquire about low endotoxin, azide-free CD103 antibody.

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com