
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-28222

NBP1-28222

CD1 Antibody (76-7-4) [FITC]



Unit Size
0.25 mg

Concentration
0.5 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
FLOW, IHC, IHC-Fr, IP

Species
Porcine

Host
Mouse

Clonality
Monoclonal

Isotype
IgG2a Kappa

Conjugate
FITC

Purity
IgG purified

Preservative
Sodium Azide

Updated 3/9/2013 2.0

Specificity/Sensitivity
Porcine CD1, Mr 43-49 kDa


Immunogen
Porcine CD1, Mw 43-49 kDa

Recommended Dilutions
Flow Cytometry < or =1 ug/10^6 cells, Immunoprecipitation, Immunohistochemistry-Frozen, Immunohistochemistry

Buffer
PBS

Uses
Flow Cytometry, Immunoprecipitation, Immunohistochemistry-Frozen

Images
Flow cytometry / FACS analysis: CD1 Antibody (76-7-4) [FITC] [NBP1-28222] - Peripheral blood mononuclear cells were isolated from heparinized pig blood on Ficoll-Paque density gradients and incubated with mouse anti-pig CD1-BIOT and mouse an... See more at www.novusbio.com/NBP1-28222



Notes
Protect conjugated forms from light.

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com