
NBP1-05962

Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-05962

NBP1-05962

EEA1 Antibody



Unit Size
0.1 ml

Concentration
0.2 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
WB, ICC/IF, IHC, IHC-P, IP

Species
Human, Mouse

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.09% Sodium Azide

Marker
Early Endosome Marker

Updated 3/9/2013 2.0


Immunogen
The immunogen recognized by this antibody maps to a region between residue 175 and 225 of human early endosome antigen 1 using the numbering given in entry NP_003557.2 (GeneID 8411).

Recommended Dilutions
Immunocytochemistry/Immunofluorescence 1:50-1:500, Immunohistochemistry 1:100-1:500, Immunohistochemistry-Paraffin 1:100-1:500, Immunoprecipitation 2-5 ug/mg lysate, Western Blot 1:2000-1:10000

Buffer
Tris-buffered Saline and 0.1% BSA

Uses
For IHC: Epitope retrieval with citrate buffer pH6.0 is recommended.

Images
Western Blot: EEA1 Antibody [NBP1-05962] - Whole cell lysate from HeLa, 293T, and mouse NIH3T3 cells. EEA1 was also immunoprecipitated by rabbit anti-EEA1 antibodies NBP1-05961 and NBP1-05963.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com