
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-02491

NBP1-02491

SHFM3 Antibody



Unit Size
0.05 mg

Concentration
Concentrations vary lot to lot. See vial label for concentration.

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
ELISA, IHC, IHC-P

Species
Human

Host
Rabbit

Clonality
Polyclonal

Purity
Protein G purified

Preservative
0.1% Sodium Azide

Updated 3/9/2013 2.0

Specificity/Sensitivity
Amino acids 157 to 171 of human FBXW4(SHFM3)


Immunogen
Synthetic peptide - KLH conjugated corresponding to Amino acids 157 to 171 of human FBXW4(SHFM3)

Recommended Dilutions
ELISA, Immunohistochemistry, Immunohistochemistry-Paraffin 10 ug/ml

Buffer
PBS

Uses
This antibody is useful for the following applications and at the following dilutions: ELISA 1:0 -1:1000, Immunohistochemistry-Paraffin 10 ug/ml

Images
Immunohistochemistry-Paraffin: SHFM3 Antibody [NBP1-02491] - Staining of human kidney. Immunohistochemistry of formalin-fixed, paraffin-embedded tissue after heat-induced antigen retrieval. Antibody concentration 10 ug/ml.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com