
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBC1-18385

# NBC1-18385

# Rac1 Protein



## Unit Size
0.1 mg

## Concentration
1.0 mg/ml

## Storage
Store at -80C. Avoid freeze-thaw cycles.

## Applications
ELISA, PAGE

## Species
Human

## Purity
Protein

## Preservative
No Preservative

Updated 3/9/2013 2.0


## Immunogen
MQAIKCVVVGDGAVGKTCLLISYTTNAFPGEYIPTVFDNYSANVMVDGKPVNLGLWDTAGQ EDYDRLRPLSYPQTDVFLICFSLVSPASFENVRAKWYPEVRHHCPNTPIILVGTKLDLRDDK DTIEKLKEKKLTPITYPQGLAMAKEIGAVKYLECSALTQRGLKTVFDEAIRAVLCPPPVKKRK RKCLLL

## Recommended Dilutions
ELISA
SDS-Page

## Buffer
Liquid. In 20mM Tris-HCl pH7.5, 2mM EDTA, 1mMDTT

## Uses
This product is useful for ELISA and SDS-Page. The purity of this protein is > 95% by SDS - PAGE. This recombinant protein was expressed in E.Coli bacteria. The endotoxin levels of this protein have not yet been determined.

## Images
SDS-Page: Rac1 Protein [NBC1-18385] - RAC1, 21.4 kDa (192 aa), confirmed by MALDI-TOF with a purity of 95% by SDS - PAGE



*Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months.* ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

**Novus USA**
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

**Novus Canada**
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

**Novus Europe**
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com