
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBC1-18502

NBC1-18502

AGR2 Protein



Unit Size
0.1 mg

Concentration
1.0 mg/ml

Storage
Store at -80C. Avoid freeze-thaw cycles.

Applications
ELISA, PAGE

Species
Human

Purity
Protein

Preservative
No Preservative

Updated 3/9/2013 2.0

Specificity/Sensitivity
This protein is from amino acids 21-175


Immunogen
MRGSHHHHHHGMASMTGGQQMGRDLYDDDDKDRWGSMRDTTVKPGAKKDTKDSRPKL PQTLSRGWGDQLIWTQTYEEALYKSKTSNKPLMIIHHLDECPHSQALKKVFAENKEIQKLAE QFVLLNLVYETTDKHLSPDGQYVPRIMFVDPSLTVRADITGRYSNRLYAYEPADTALLLDNM KKALKLLKTEL

Recommended Dilutions
ELISA
SDS-Page

Buffer
20mM Tris 8.0, 1mM DTT, 10% glycerol, 1mM EDTA

Uses
This product is useful as positive control for ELISA and SDS-Page. Purity is > 95 % by SDS-Page.

Images
SDS-Page: AGR2 Protein [NBC1-18502] - AGR 2, 22 kDa (192 aa), confirmed by MALDI-TOF with a purity of 95% by SDS - PAGE



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com