
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB600-1456

NB600-1456

Osteocalcin Antibody



Unit Size
0.05 ml

Concentration
This product is unpurified. The exact concentration of antibody is not quantifiable.

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
ELISA, RIA

Species
Human

Host
Rabbit

Clonality
Polyclonal

Purity
Whole antisera

Preservative
No Preservative

Updated 3/9/2013 2.0

Specificity/Sensitivity
There were no cross reactivities obtained with human Osteopontin, human Osteonectin, and human Bone Sialoprotein.

Immunogen
Synthetic peptide: MRALTLLALLALAALCIAGQAG, corresponding to amino acids 1-22 of Human Osteocalcin.

Recommended Dilutions
ELISA 1:5000, Radioimmunoassay 1:2000

Buffer
Whole Serum

Uses
This antibody is useful for ELISA.

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB600-1456

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com